

JUMBO Filtertrolley 2.0



ULTJUMBO®

Version: 02

Dated: 11/2022



LASER FUMES



DUST AND SMOKE



SOLDERING FUMES



ODORS, GASES, AND VAPORS



CLEANING INDUSTRIAL GASES



NEW EMISSIONS



WELDING FUMES



OIL AND EMULSION MISTS



COMPLETE SOLUTIONS



JUMBO Filtertrolley 2.0



Accessory articles

Devices	3
DN50 extraction system.....	5
DN75 extraction system.....	6
Interface accessories.....	7
Replacement filter	8

In conjunction with their filters, the JUMBO Filtertrolley 2.0 filter devices offer a specific solution for all extraction purposes

ULT AG offers a range of selected suction hoses and accessories for individually configuring the JUMBO Filtertrolley 2.0. The product range includes DN50 and DN75 diameters.

The JUMBO Filtertrolley 2.0 can be operated with an extraction arm from the Danish manufacturer Alsident®. The practical mounting console allows an extraction arm to be mounted directly on the device. A range of System 50 and System 75 extraction arms are available for the device.

To ensure full capture, you can select collecting elements matching the pollution source. The range includes suction tips, suction gaps, round hoods and flat hoods. For small, concentrated sources of contamination, a suction tip is recommended which sucks close to the source without impeding the working view. For larger sources of pollutants, like soldering, the use of a suction gap is suitable. Round hoods are recommended for the extraction of light smoke and rising gases and are positioned vertically above the source. For the extraction of heavy gases and for open containers, a flat hood is recommended, which has a particularly good performance in vertical position on a surface, for example a table.

For worldwide operation, ULT provides country-specific power cables free of charge: in addition to the standard European CEE 7/7 cable, these also include Swiss, UK and US cables as desired.



JUMBO Filtertrolley 2.0



Devices

The accessory portfolio relates to the following devices:

ACD – Odor, Gas and Vapors



Filtertrolley 2.0 ACD	80 m ³ /h - VF	ACD Jumbo 2.0-BM.3.0
100-120 V 50% Chemisorption 100% Chemisorption		9-00116 9-00117 9-00118

ASD – Dust and Smoke



Filtertrolley 2.0 ASD	80 m ³ /h - VF	ASD Jumbo 2.0-BM.3.0
100-120 V		9-00116

LAS – Laser Fumes



Filtertrolley 2.0 LAS	80 m ³ /h - VF	LAS Jumbo 2.0-BM.3.0
100-120 V		9-00116

LRA – Soldering Smoke




Filtertrolley 2.0 LRA	80 m ³ /h - VF	LRA Jumbo 2.0-BM.3.0
100-120 V		9-00116

LabCat – Laboratory applications



Filtertrolley 2.0 LabCat K	80 m ³ /h - VF	LabCat Jumbo 2.0BM.3.6017
100-120 V		9-00116
Filtertrolley 2.0 LabCat A	80 m ³ /h - VF	LabCat Jumbo 2.0BM.3.1000
100-120 V 50% Chemisorption 100% Chemisorption		9-00116 9-00117 9-00118

JUMBO Filtertrolley 2.0



Devices

MED – medical laser fumes



Filtertrolley 2.0 MED 100-120 V	80 m³/h - VF	MED Jumbo 2.0-BM.3.0 9-00116
Filtertrolley 2.0 MED Kit (extraction arm included) 100-120 V	80 m³/h - VF	MED Jumbo 2.0-BM.9.0 9-00116

Restauro – Dusts, smokes, vapours



Filtertrolley 2.0 Restauro 100-120 V	80 m³/h - VF	RES Jumbo 2.0-BM.3.0 9-00116
---	--------------	---------------------------------

JUMBO Filtertrolley 2.0

DN50 extraction system

Hoses



Suction hose DN 50, per meter	antistatic, without accessories	6-06757
Suction hose DN 50, 2 meter	antistatic, with adapter piece	3-00430
Suction hose DN 50, 3 meter	antistatic, with adapter piece	3-00431
Suction hose DN 50, 5 meter	antistatic, with adapter piece	3-00432

Hose accessories



Tail DN 50	antistatic, connection device to hose	3-00434
------------	---------------------------------------	---------

Extraction arms



Alsident system 50, antistatic extraction arm	945 mm for table/device mounting	50-4737-1-6
---	----------------------------------	-------------

Collecting elements



Flat screen antistatic	Alsident System 50, accessory	1-503324-6
Round hood aluminium antistatic	Alsident System 50, accessory	1-5024-6
Extractor tube antistatic	Alsident System 50, accessory	1-5021-6
Suction gap antistatic	Alsident System 50, accessory	1-5020-6

JUMBO Filtertrolley 2.0



DN75 extraction system

Hose



extraction hose DN 75, per meter	Antistatic, without accessories	6-06748
----------------------------------	---------------------------------	---------

Hose accessories



Tail DN 75	Antistatic	3-00457
------------	------------	---------



Pièce en Y DN 75 - 50	Antistatic	6-02939
-----------------------	------------	---------



worm drive hose clip	70 – 90 mm	6-06918
----------------------	------------	---------

Extraction arms



Alsident System 75, extraction arm	1290mm for table/device mounting	75-6555-1-5
------------------------------------	----------------------------------	-------------

Collecting elements



Flat screen	Alsident System 75, accessory	1-753324-5
-------------	-------------------------------	------------



Round hood aluminium	Alsident System 75, accessory	1-7524-5
----------------------	-------------------------------	----------



Extractor tube	Alsident System 75, accessory	1-7525
----------------	-------------------------------	--------

Interface accessories

Device power cables – supplied free of charge with ordered device




Swiss device power cable	Length 3.00 m	6-06056
UK device power cable	Length 2.00 m	6-06063
USA device power cable	Length 2.00 m	6-06091
EU device power cable (CEE 7/7)	Lenght 3,00 m	6-05990

JUMBO Filtertrolley 2.0




Replacement filter

ACD




Filter A6

Adsorption filter cassette A6	4-00378
-------------------------------	---------



Filter AC8


Chemisorption filtercassette AC8	4-00404
----------------------------------	---------



Filter C10


Chemisorption filter cassette C10	4-00402
-----------------------------------	---------

ASD



Z-Line filter cassette G4 - set of 10 pcs	4-00048
Replacement frame with Filter mat M5	4-00263
Particle filter cassette H13	4-00020


LAS



Filter K

Expanded metal	4-00295
Replacement frame with Filter mats M5/F7	4-00262
Combined filter cassette H13A	4-00046

LRA




Filter K

Expanded metal	4-00295
Replacement frame with Filter mats M5/F7	4-00262
Combined filter cassette H13A	4-00046


Replacement filter

LabCat




Filter A6

Adsorption filter cassette A6	4-00378
-------------------------------	---------




Filter AC8

Chemisorption filtercassette AC8	4-00404
----------------------------------	---------



Filter C10


Chemisorption filter cassette C10	4-00402
-----------------------------------	---------



Filter K

Z-Line filter cassette G4 -set of 10 pcs	4-00054
Filter mat M5 - set of 10 pcs	4-00232
Combined filter cassette H13A	4-00050


MED



Filter U15A

Z-Line filter cassette G4 -set of 10 pcs	4-00054
Filter mat M5 - set of 10 pcs	4-00232
Combined filter cassette U15A	4-00052

Restauro



Filter K

Z-Line filter cassette G4 -set of 10 pcs	4-00054
Filter mat M5 - set of 10 pcs	4-00232
Combined filter cassette H13A	4-00050